

Product data sheet

Characteristics

10DWP-WE

SOCKET AUTO DP W/PROOF 10A



Main

Range of product	Standard Series
Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1

Complementary

Colour code	WE
Local signalling	Without light indicator
Device mounting	Flush
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	26 mm
Length	93 mm
Width	82 mm
Fixing center	70 x 54 mm
Number of poles	2

Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
IP degree of protection	IP44

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.128 kg
Package 1 Height	2.6 cm
Package 1 width	8.2 cm
Package 1 Length	9.3 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	648.0 g
Package 2 Height	12.6 cm
Package 2 width	14.4 cm
Package 2 Length	15.6 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	50

Package 3 Weight	6.6 kg
Package 3 Height	30.2 cm
Package 3 width	35 cm
Package 3 Length	35 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile