

## Product data sheet

### Characteristics

# 10MD15S-WE

## SWITCHED SOCKET MECHANISM DOUBLE POLE 15A SHUTTER



### Main

Range of product	Standard Series
Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

### Complementary

Colour code	WE
Marking	Without marking
Protection type	Fingersafe
Local signalling	Without light indicator
Device mounting	Flush
Fixing mode	By screws
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC
Depth	29 mm
Length	97 mm
Width	43 mm
Fixing center	84 mm
Number of poles	2

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	57 g
Package 1 Height	3.7 cm
Package 1 width	4.5 cm
Package 1 Length	9.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	320 g
Package 2 Height	8.2 cm
Package 2 width	17.5 cm

Package 2 Length	27.1 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	6.4 kg
Package 3 Height	25 cm
Package 3 width	21.4 cm
Package 3 Length	33.8 cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>