

## Product data sheet

### Characteristics

# 10MDP-WE

## Automatic Single Socket Outlet Mechanism, Standard Series, 250VAC, 10A, 2 Pole, Panel Mount

### Main

Range of product	Standard Series
Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

### Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Flush
Fixing mode	By screws
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	33 mm
Length	43 mm
Width	42 mm
Fixing center	84 mm
Number of poles	2

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	4.2 cm
Package 1 Length	4.4 cm
Package 1 Weight	52 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	10.6 cm
Package 2 Width	12.2 cm
Package 2 Length	14.2 cm
Package 2 Weight	438 g

## Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Take-back	No