

Product data sheet

Characteristics

1438-TR

SOCKET CORD EXTENSION 10A 250V



Main

Range of product	Standard Series
Product or component type	Socket-outlet
Colour	Transparent
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	TR
Marking	Without marking
Local signalling	Without light indicator
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	62 mm
Diameter	41 mm

Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	48.3 g
Package 1 Height	50 mm
Package 1 width	70 mm
Package 1 Length	100 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	0.55 kg
Package 2 Height	84 mm
Package 2 width	126.5 mm
Package 2 Length	170 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Weight	11 kg
Package 3 Height	254 mm
Package 3 width	348 mm
Package 3 Length	445 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile