

Product data sheet

Characteristics

1438-TR

SOCKET CORD EXTENSION 10A 250V



Main

Range of product	Standard Series
Colour	Transparent
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	TR
Marking	Without marking
Local signalling	Without light indicator
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	62 mm
Diameter	41 mm




Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	48.3 g
Package 1 Height	50 mm
Package 1 width	70 mm
Package 1 Length	100 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	0.55 kg
Package 2 Height	84 mm
Package 2 width	126.5 mm
Package 2 Length	170 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Weight	11 kg
Package 3 Height	254 mm
Package 3 width	348 mm
Package 3 Length	445 mm

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration