

Product data sheet

Characteristics

15/15N-WE

Single Switch Socket Outlet, Standard Series, 250V, 15A, Standard Size, 1 Pole, Neon

Main

Range of product	Standard Series
Product or component type	Switched socket
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number Of Outlets	1
Actuator	Switch Rocker
Mounting Type	By screws
Local signalling	Indicator light
Installation Orientation	Horizontal
Material	PC (polycarbonate)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	15 A
Depth	14 mm
Length	115 mm
Width	73 mm
Mounting Centers	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.4 cm
Package 1 Width	7.3 cm
Package 1 Length	11.5 cm
Package 1 Weight	0.1 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	5

Package 2 Height	11.7 cm
Package 2 Width	10.2 cm
Package 2 Length	13.8 cm
Package 2 Weight	500 g
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	15.7 cm
Package 3 Width	30.5 cm
Package 3 Length	44.5 cm
Package 3 Weight	5 kg

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations