

## Product data sheet

### Characteristics

# 15D-WE

## SWITCHED SOCKET SINGLE DOUBLE POLE

### 10A 250V



#### Main

Range of product	Standard Series
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

#### Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Rocker Switch
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	PC (polycarbonate)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	14 mm
Length	115 mm
Width	73 mm
Fixing center	84 mm

#### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1
-----------	--

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	83 g
Package 1 Height	72 mm
Package 1 width	35 mm
Package 1 Length	115 mm
Unit Type of Package 2	BB1

Number of Units in Package 2	5
Package 2 Weight	0.452 kg
Package 2 Height	106 mm
Package 2 width	124 mm
Package 2 Length	142 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	9.2 kg
Package 3 Height	254 mm
Package 3 width	348 mm
Package 3 Length	445 mm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>