

Product data sheet

Characteristics

15VS-WE

SOCKET SWITCHED SINGLE VERTICAL MOUNT 10A WITH SAFETY SHUTTER



Main

Range of product	Standard Series
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Vertical
Material	PC (polycarbonate)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	14 mm
Length	115 mm
Width	73 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.082 kg
Package 1 Height	14 mm
Package 1 width	73 mm
Package 1 Length	115 mm
Unit Type of Package 2	BB1

Number of Units in Package 2	10
Package 2 Weight	0.82 kg
Package 2 Height	118 mm
Package 2 width	148 mm
Package 2 Length	167 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	8.2 kg
Package 3 Height	254 mm
Package 3 width	348 mm
Package 3 Length	445 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile