

Product data sheet

Characteristics

16-WE

SOCKET SWITCHED SINGLE 10A SKIRTING MOUNT



Main

Range of product	Standard Series
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	14 mm
Length	98 mm
Width	45 mm
Fixing center	78 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	62.0 g
Package 1 Height	2.5 cm
Package 1 width	4.5 cm
Package 1 Length	10 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10

Package 2 Weight	660.0 g
Package 2 Height	7.7 cm
Package 2 width	10.5 cm
Package 2 Length	19.5 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	6.2 kg
Package 3 Height	25 cm
Package 3 width	21.4 cm
Package 3 Length	33.8 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile