

Product data sheet

Characteristics

2015V15N-WE

SOCKET SWITCHED SINGLE VERTICAL MOUNT 15A NEON



Main

Colour	White electric
Product brand	Clipsal
Range of product	Series 2000

Complementary

Colour code	WE
Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Rocker Switch
Mounting position	Vertical
Fixing mode	By screws
Local signalling	Indicator light
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	15 A
Depth	12 mm
Length	116 mm
Width	76 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.096 kg
Package 1 Height	12 mm
Package 1 width	76 mm
Package 1 Length	116 mm
Unit Type of Package 2	BB1

Number of Units in Package 2	10
Package 2 Weight	0.96 kg
Package 2 Height	122 mm
Package 2 width	141 mm
Package 2 Length	161 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	9.6 kg
Package 3 Height	254 mm
Package 3 width	348 mm
Package 3 Length	445 mm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile