

## Product data sheet

### Characteristics

# 2031VA-WE

## 2000 Series, Flush Switch 1 Gang, 250VAC, 10A, Standard, Vertical



### Main

Range of product	Series 2000
Product brand	Clipsal
Assembly Type	Basic element with full cover plate and grid

### Complementary

Number of poles	1
Installation Type	Flush
Number Of Switches	1
Material	PC (polycarbonate)
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A 8 AX, fluorescent lamp
Marking	Without marking
Mounting Type	By screws
Surface finish	Glossy
Actuator	Rocker
Switch function	1-pole

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	7 cm
Package 1 Length	11.4 cm
Package 1 Weight	67 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	12.6 cm
Package 2 Width	15 cm
Package 2 Length	16.4 cm
Package 2 Weight	732 g
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	27 cm
Package 3 Width	35.4 cm

Package 3 Length	45.1 cm
Package 3 Weight	7.888 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations