

Product data sheet

Characteristics

2032V66-WE

Flush Switch, 2000 Series, 2 Gang, 250VAC, 10A, Weatherproof, Vertical



Main

Range of product	Series 2000
Product brand	Clipsal
Assembly Type	Basic element with full cover plate and grid

Complementary

Installation Type	Flush
Number Of Switches	2
Material	PC (polycarbonate)
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A 10 AX, fluorescent lamp
Marking	Without marking
Mounting Type	By screws
Actuator	Rocker
Switch function	2-way 1-way

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	7.7 cm
Package 1 Length	12.2 cm
Package 1 Weight	138.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations