

Product data sheet

Characteristics

247/20-EO

Clipsal - Cable Management, Solid Fittings - PVC, Solid Elbows, BEnds, 20mm



Main

| | |
|------------------|-----------------|
| Colour | Electric orange |
| Product brand | Clipsal |
| Range of product | Series 247 |

Complementary

| | |
|-----------------|--------------------------|
| Colour code | EO |
| Material | PVC (polyvinyl chloride) |
| Diameter | 20 mm |
| Operating angle | 90 ° |
| Length | 83 mm |
| Inner radius | 47 mm |

Environment

| | |
|-----------|-------------|
| Standards | AS/NZS 2053 |
|-----------|-------------|

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 2.7 cm |
| Package 1 Width | 2.7 cm |
| Package 1 Length | 11.5 cm |
| Package 1 Weight | 26 g |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |
| Circularity Profile | No need of specific recycling operations |