

Product data sheet

Characteristics

247L25-EO

Conduit Bend, Clipsal - Cable Management, Large Sweep, 90Deg, PVC, 25mm



Main

| | |
|------------------|-----------------|
| Colour | Electric orange |
| Product brand | Clipsal |
| Range of product | Series 247L |

Complementary

| | |
|-----------------|--------------------------|
| Colour code | EO |
| Material | PVC (polyvinyl chloride) |
| Diameter | 25 mm |
| Operating angle | 90 ° |
| Length | 192 mm |
| Inner radius | 150 mm |

Environment

| | |
|-----------|-------------|
| Standards | AS/NZS 2053 |
|-----------|-------------|

Packing Units

| | |
|------------------------------|-------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3 cm |
| Package 1 Width | 9 cm |
| Package 1 Length | 28 cm |
| Package 1 Weight | 89 g |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |