

Product data sheet

Characteristics

247L32-EO

BEND CONDUIT 90 DEGREE LESS ENCLOSURES WP 32MM. 247L32,EO REPLACES GET247L32,EO.



Main

Colour	Electric orange
Product brand	Clipsal
Range of product	Series 247L

Complementary

Colour code	EO
Material	PVC (polyvinyl chloride)
Diameter	32 mm
Operating angle	90 °
Length	350 mm
Inner radius	312 mm

Environment

Standards	AS/NZS 2053
-----------	-------------

Packing Units

Package 1 Weight	216.000 g
Package 1 Height	38.000 mm
Package 1 width	45.000 mm
Package 1 Length	515.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile