

Product data sheet

Characteristics

247LH20-EO

BEND CONDUIT 45 DEGREE LESS ENCLOSURE SWP 20 MM - Electric Orange



Main

Colour	Electric orange
Product brand	Clipsal
Range of product	Series 247L

Complementary

Colour code	EO
Material	PVC (polyvinyl chloride)
Diameter	20 mm
Operating angle	45 °
Length	145 mm
Inner radius	150 mm

Environment

Standards	AS/NZS 2053
-----------	-------------

Packing Units

Package 1 Weight	0.050 kg
Package 1 Height	25.000 mm
Package 1 width	25.000 mm
Package 1 Length	195.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile