

# Product data sheet

## Characteristics

# 25/15-WE

## SWITCHED SOCKET TWIN STANDARD PTN 15A



### Main

Range of product	Standard Series
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

### Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	PC (polycarbonate)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	15 A
Depth	16 mm
Length	115 mm
Width	73 mm
Fixing center	84 mm

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1
-----------	--

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.101 kg
Package 1 Height	3 cm
Package 1 width	7.3 cm
Package 1 Length	11.5 cm
Unit Type of Package 2	CAR

Number of Units in Package 2	100
Package 2 Weight	11.66 kg
Package 2 Height	25.4 cm
Package 2 width	34.8 cm
Package 2 Length	44.5 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	5
Package 3 Weight	0.558 kg
Package 3 Height	11.7 cm
Package 3 width	10.2 cm
Package 3 Length	13.8 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>