

Product data sheet

Characteristics

263/40-EO

Clipsal - Cable Management, Solid Fittings - PVC, Adaptors - Plain to Screwed Conduit, 40mm



Main

Colour	Electric orange
Product brand	Clipsal
Range of product	Series 263

Complementary

Colour code	EO
Material	PVC (polyvinyl chloride)
Connector type	Thread connector
Product destination	Diameter: 40 mm tube
Length	58 mm

Environment

Standards	AS/NZS 2053
-----------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.6 cm
Package 1 Width	4.6 cm
Package 1 Length	5.2 cm
Package 1 Weight	27.4 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	85 cm
Package 2 Width	97 cm
Package 2 Length	150 cm
Package 2 Weight	274 g
Unit Type of Package 3	PAL
Number of Units in Package 3	6000
Package 3 Height	140 cm
Package 3 Width	114 cm
Package 3 Length	114 cm
Package 3 Weight	180 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations