



### Main

Colour	Grey
Product brand	Clipsal
Range of product	Series 279AC
Product or component type	Elbow

### Complementary

Colour code	GY
Thread type	M25
Threaded length	1.5 mm
Cable outer diameter	25 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Operating angle	90 °




### Environment

IP degree of protection	IP54
Ambient air temperature for operation	-15...65 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	44 g
Package 1 Height	35 mm
Package 1 width	35 mm
Package 1 Length	82 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>

---

China RoHS Regulation

[China RoHS Declaration](#)

---

Environmental Disclosure

[Product Environmental Profile](#)

---