

Product data sheet

Characteristics

279C50-GY

Straight Gland, Clipsal - Cable Management, 50mm

Main

Colour	Grey
Product brand	Clipsal
Range of product	Series 279C
Tool type	66 mm wrench

Complementary

Colour code	GY
Thread type	M50
Threaded length	1.5 mm
Cable outer diameter	50 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Installation direction	Straight

Environment

Ambient air temperature for operation	-15...65 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	5.8 cm
Package 1 Length	7.2 cm
Package 1 Weight	76.0 g

Offer Sustainability

Packaging without single use plastic	Yes
Packaging made with recycled cardboard	Yes
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Circularity Profile	No need of specific recycling operations
Take-back	No
