

Product data sheet

Characteristics

2D4P6AIPV3R-BU

CBL LAN CAT6A -305M REEL



Main

Range of product	Titanium
Product brand	Clipsal
Colour	External sheath: blue

Complementary

Communication network category	6A
AWG gauge	AWG 23
Cable shielding type	UTP
Cable insulation material	PVC (polyvinyl chloride)
Material	Conductor: bare copper
Diameter	0.59 mm (conductor)
External diameter	8.5 mm
Length	305 m
Colour code	BU

Environment

Ambient air temperature for operation	75 °C
Flame retardance	CM
Marking	Colour coding
Product certifications	UL listed file E197794
Standards	ISO/IEC 11801 EIA/TIA-568 IEC 61156-5

Packing Units

Package 1 Weight	0.077 kg
------------------	----------

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.