

## Product data sheet

### Characteristics

# 30/2NM-WE

## Switch Mechanism, 30 Series, 250V, 10A, 2 Way, with Neon Indicator



### Main

Range of product	Standard Series Series 30
Product brand	Clipsal
Assembly Type	Basic element

### Complementary

Number of poles	1
Installation Type	Flush
Number Of Switches	1
Material	PVC (polyvinyl chloride)
Local signalling	neon
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Load type	Fluorescent 100 W 10 A LEDi lamp 100 W 10 A
Marking	Without marking
Surface finish	Glossy
Actuator	Rocker
Switch function	1-pole

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.4 cm
Package 1 Width	2.5 cm
Package 1 Length	3.5 cm
Package 1 Weight	20 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>

