

Product data sheet

Characteristics

3015/4C-XW

Quad Power Point Skin, Clipsal Iconic, Horizontal Mount, 250V, 10A, Clip-On

Main

Range of product	Iconic
Range	Clipsal Iconic
Aesthetic name	Iconic
Product or component type	Skin
Colour tint	Vivid white
Colour tint	White (XW)
Type of packing	Polybag
Quantity per set	Set of 10

Complementary

Range compatibility	Clipsal Iconic switched socket
Product destination	Switched socket
Device mounting	Flush
Number of rocker	4
Number of power socket outlets	4
[In] rated current	10 A
Installation direction	Horizontal
Fixing mode	Clip-on
Surface finish	Matt
Surface treatment	Untreated
Built-in height	78 mm
Built-in width	216 mm
Material	PC (polycarbonate): skin ABS (acrylonitrile butadiene-styrene): skin
Height	216 mm
Width	78 mm
Depth	9 mm
Net weight	0.02 kg

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.9 cm
Package 1 Width	7.8 cm
Package 1 Length	21.7 cm
Package 1 Weight	41 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10

Package 2 Height	10.4 cm
Package 2 Width	14.4 cm
Package 2 Length	22 cm
Package 2 Weight	508 g

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1

Contractual warranty

Warranty	1 year
----------	--------