

# Product data sheet

## Characteristics

# 30M35-WE

## SWITCH MECH 35A 250V



### Main

Range of product	Standard Series Series 30
Product brand	Clipsal
Device presentation	Basic element

### Complementary

Switch function	1-pole
Number of rocker	1
Number of poles	1
Device mounting	Flush
Material	PVC (polyvinyl chloride)
Surface finish	Glossy
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	35 A
Marking	Without marking
Marking location	Marking on surface
Actuator	Rocker

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	16.5 g
Package 1 Height	2.36 cm
Package 1 width	2.36 cm
Package 1 Length	2.9 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	0.093 kg
Package 2 Height	3.4 cm
Package 2 width	5.2 cm
Package 2 Length	7.3 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	0.988 kg
Package 3 Height	10.2 cm
Package 3 width	12 cm
Package 3 Length	17 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>