

Product data sheet

Characteristics

30M35OV-WE

Switch Mechanism, 30 Series, 35A, Marked OVEN



Main

Range of product	Series 30 Standard Series
Product brand	Clipsal
Assembly Type	Basic element



Complementary

Number of poles	1
Installation Type	Flush
Number Of Switches	1
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	35 A
Marking	Oven
Marking location	Marking on surface
Mounting Type	Clip-in
Surface finish	Glossy
Actuator	Rocker
Switch function	1-pole

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.36 cm
Package 1 Width	2.36 cm
Package 1 Length	2.9 cm
Package 1 Weight	16.5 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

