

Product data sheet

Characteristics

30MBPR-WE

Bell Rocker, Clipsal - Mechanisms, Marked "PRESS", 250V, 10A



Main

Range of product	Standard Series Series 30
Product brand	Clipsal
Assembly Type	Basic element

Complementary

Installation Type	Flush
Number Of Switches	1
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Press
Marking location	Marking on surface
Mounting Type	Clip-in
Actuator	Rocker

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.36 cm
Package 1 Width	2.36 cm
Package 1 Length	2.9 cm
Package 1 Weight	14.4 g
Unit Type of Package 2	CAR
Number of Units in Package 2	125
Package 2 Height	117 cm
Package 2 Width	250 cm
Package 2 Length	310 cm
Package 2 Weight	2.6 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations