

Product data sheet

Characteristics

30MI-WE

Switch 30 Series Mechanism - Intermediate - 250 V - 10 A - White Electric



Main

Range of product	Series 30 Standard Series
Product brand	Clipsal
Device presentation	Basic element

Complementary

Switch function	1-pole
Actuator	Rocker
Number of rocker	1
Number of poles	1
Device mounting	Flush
Material	PVC (polyvinyl chloride)
Surface finish	Glossy
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	16 g
Package 1 Height	2.3 cm
Package 1 width	2.2 cm
Package 1 Length	2.9 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	90 g
Package 2 Height	3.8 cm
Package 2 width	5.2 cm
Package 2 Length	7.4 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	1 kg
Package 3 Height	10.2 cm
Package 3 width	12 cm
Package 3 Length	17 cm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile