

## Product data sheet

### Characteristics

# 30MI-WE

## Switch 30 Series Mechanism - Intermediate - 250 V - 10 A - White Electric



### Main

Range of product	Series 30 Standard Series
Product brand	Clipsal
Device presentation	Basic element

### Complementary

Switch function	1-pole
Number of rocker	1
Number of poles	1
Device mounting	Flush
Material	PVC (polyvinyl chloride)
Surface finish	Glossy
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Load type	Fluorescent lamp 10 A LEDi lamp 100 W
Marking	Without marking
Actuator	Rocker

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	16.0 g
Package 1 Height	2.3 cm
Package 1 width	2.2 cm
Package 1 Length	2.9 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	90.0 g
Package 2 Height	3.8 cm
Package 2 width	5.2 cm
Package 2 Length	7.4 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	1.0 kg
Package 3 Height	10.2 cm

Package 3 width	12 cm
Package 3 Length	17 cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>