

Product data sheet

Characteristics

30RJ45SM6AF

Clipsal Actassi, Socket Module Connector, Rj45, Cat6A, Shielded 30 Mech



Main

Product brand	Clipsal
Range of product	Titanium
Product or component type	Modular jack

Complementary

Connector type	RJ45
Communication network category	6A
AWG gauge	AWG 24...AWG 22
[In] rated current	2 A
Material	Phosphor bronze
Depth	41 mm
Width	23 mm
Height	26 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	8.0 cm
Package 1 Length	6.0 cm
Package 1 Weight	38.9 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations