

# Product data sheet

## Characteristics

# 39MAOM-WE

## Switch, Clipsal - Mechanisms, 1 Pole, 250VAC, 10A, Auto/Off/Man



### Main

Range of product	Series 30 Standard Series
Product brand	Clipsal
Assembly Type	Basic element

### Complementary

Control type	Rotary knob
Number of poles	1
Installation Type	Flush
Number Of Switches	1
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Load type	Fluorescent lamp 10 A LEDi lamp 100 W
Marking	AUTO-O-MAN
Marking location	Marking on surface
Mounting Type	Clip-in
Surface finish	Glossy
Switch function	1-pole

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.3 cm
Package 1 Width	2.2 cm
Package 1 Length	3.2 cm
Package 1 Weight	15.2 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

---

RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

---