

Product data sheet

Characteristics

39MUOD-WE

Clipsal - Mechanisms, Switch Mechanism 3

Pos Up / Off / Down



Main

Range of product	Standard Series Series 30
Product brand	Clipsal
Assembly Type	Basic element

Complementary

Control type	Rotary knob
Installation Type	Flush
Number Of Switches	1
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Load type	Fluorescent lamp 10 A LEDi lamp 100 W
Marking	UP-OFF-DOWN
Marking location	Marking on surface

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.3 cm
Package 1 Width	2.2 cm
Package 1 Length	3.2 cm
Package 1 Weight	15.2 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4 cm
Package 2 Width	5.8 cm
Package 2 Length	11.6 cm
Package 2 Weight	150 g
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	10.2 cm
Package 3 Width	12 cm
Package 3 Length	17 cm
Package 3 Weight	700 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations