

Product data sheet

Characteristics

402-WE

Single Socket Outlet, Standard Series, 125VAC, 10A, 2 PIN ParAllel, Surface Mount

Main

Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Surface
Fixing mode	By screws
[In] rated current	10 A
[Ue] rated operational voltage	110 V AC
Depth	28 mm
Diameter	45 mm
Fixing center	28 mm
Number of poles	1



Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	4.1 cm
Package 1 Length	4.1 cm
Package 1 Weight	32 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes