

# Product data sheet

## Characteristics

# 402/32-WE

## SOCKET 2PIN FLAT 32VOLT



### Main

Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

### Complementary

Colour code	WE
Marking	Extra low voltage
Local signalling	Without light indicator
Device mounting	Surface
Fixing mode	By screws
Material	Plastic
[In] rated current	15 A
[Ue] rated operational voltage	32 V DC
Network frequency	50 Hz
Depth	28 mm
Diameter	47 mm
Fixing center	35...38 mm
Number of poles	1

### Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

### Packing Units

Package 1 Weight	33 g
------------------	------

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>