

Product data sheet

Characteristics

4025H2-HS

Quad Switch Power Point, Saturn Series, 250V, 10A



Main

Range of product	Saturn Series
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	4 gangs
Pin number	3
Number Of Outlets	4
Actuator	Switch Rocker
Mounting Type	By screws
Local signalling	Without light indicator
Installation Orientation	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Embedding depth	15 mm
Depth	29 mm
Height	75 mm
Length	232 mm
Width	232 mm
Mounting Centers	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.3 cm
Package 1 Width	8.5 cm
Package 1 Length	23.2 cm

Package 1 Weight	288 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	9 cm
Package 2 Width	19 cm
Package 2 Length	24 cm
Package 2 Weight	1.58 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	End Of Life Information