

## Product data sheet

### Characteristics

# 4025X-HS

## Double Switch Power Point, Saturn Series, 250V, 10A, Non-removable, Extra Switch



### Main

Range of product	Saturn Series
Product brand	Clipsal

### Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number Of Outlets	2
Actuator	Rocker Switch
Mounting Type	By screws
Local signalling	Without light indicator
Installation Orientation	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Embedding depth	15 mm
Depth	29 mm
Height	75 mm
Length	116 mm
Width	116 mm
Mounting Centers	84 mm

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	7.5 cm
Package 1 Length	11.7 cm

Package 1 Weight	140.9 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	12.8 cm
Package 2 Width	18.4 cm
Package 2 Length	19.2 cm
Package 2 Weight	1.514 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations