

Product data sheet

Characteristics

4025X-HS

Socket Outlet Saturn - Twin switched - Assembled - Extra switch - Horizontal - 250 V - 10 A - Horizon Silver



Main

Colour	Horizon silver
Product brand	Clipsal
Range of product	Saturn Series

Complementary

Colour code	HS
Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Rocker Switch
Mounting position	Horizontal
Fixing mode	By screws
Local signalling	Without light indicator
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	29 mm
Embedding depth	15 mm
Length	116 mm
Width	116 mm
Height	75 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Package 1 Weight	140.9 g
Package 2 Weight	1.514 kg
Package 3 Weight	3 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile