

Product data sheet

Characteristics

4061/45-HS

Flush Switch, Saturn Series, 1 Gang, 250V, AC,45A, Push Button



Main

Range of product	Saturn Series 4000
Product brand	Clipsal
Assembly Type	Basic element

Complementary

Number of poles	1
Installation Type	Flush
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	45 A
Marking	Without marking
Mounting Type	By screws
Height	116 mm
Width	75 mm
Depth	37 mm
Embedding depth	23 mm
Switch function	1-pole

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	9.5 cm
Package 1 Length	12.3 cm
Package 1 Weight	256 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	12.6 cm
Package 2 Width	10 cm
Package 2 Length	36.6 cm
Package 2 Weight	1.398 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes