

# Product data sheet

## Characteristics

# 4061/45-HS

Clipsal Saturn 4000, Flush Switch, 1 Gang, 250V, AC, 45A, Push Button



## Main

Range of product	Saturn Series 4000
Product brand	Clipsal
Assembly Type	Basic element

## Complementary

Number of poles	1
Installation Type	Flush
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	45 A
Marking	Without marking
Mounting Type	By screws
Height	116 mm
Width	75 mm
Depth	37 mm
Embedding depth	23 mm
Switch function	1-pole

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	9.5 cm
Package 1 Length	12.3 cm
Package 1 Weight	256 g

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>