

## Product data sheet

### Characteristics

# 4061/45-HS

## Switch Saturn - Cooker - Assembled - Single-pole - 250 V - 45 A - Horizon Silver



### Main

Range of product	Saturn Series 4000
Product brand	Clipsal
Device presentation	Basic element

### Complementary

Switch function	1-pole
Number of poles	1
Device mounting	Flush
Fixing mode	By screws
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	45 A
Marking	Without marking
Height	116 mm
Width	75 mm
Depth	37 mm
Embedding depth	23 mm

### Packing Units

Unit Type of Package 1	PCE
------------------------	-----

### Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.