

Product data sheet

Characteristics

4061VF3CSF-HS

Clipsal Saturn 4000, Fan Speed Controller, 3 Speed, 240V, 75VA



Main

Range of product	Saturn Series 4000
Product brand	Clipsal
Device presentation	Basic element
Load type	Capacitive

Complementary

Power consumption in VA	75 VA
Network frequency	50 Hz
Mounting support	Wall
Fixing mode	By screws
Width	75 mm
Height	116 mm
Depth	56 mm
Embedding depth	34 mm

Environment

Standards	AS/NZS CISPR 15:2002
-----------	----------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	9.4 cm
Package 1 Length	12 cm
Package 1 Weight	259.4 g

Offer Sustainability

EU RoHS Directive	Will be compliant – Date to be confirmed
-------------------	--

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.