

Product data sheet

Characteristics

4062AL-HS

Switch Saturn - Assembled - LED indicator - Architrave - 2-gang - 250 V - 20 A / 16 AX - Horizon Silver



Main

Range of product	Saturn Series 4000
Product or component type	Push-button
Colour	Horizon silver
Product brand	Clipsal
Device presentation	Basic element with full cover plate




Complementary

Colour code	HS
Actuator	Push-button
Local signalling	Indicator light
Fixing mode	By screws
Material	PVC (polyvinyl chloride)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
Inrush current	20 A
Height	97.5 mm
Depth	43.6 mm
Embedding depth	31.6 mm
Width	34 mm
Mounting position	Vertical

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	95.0 g
Package 1 Height	5 cm
Package 1 width	4 cm
Package 1 Length	10 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation

 [China RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)
