

Product data sheet

Characteristics

4062AL-HS

Switch Saturn - Assembled - LED indicator -
Architrave - 2-gang - 250 V - 20 A / 16 AX -
Horizon Silver



Main

Range of product	Saturn Series 4000
Product or component type	Push-button
Colour	Horizon silver
Product brand	Clipsal
Device presentation	Basic element with full cover plate

Complementary

Colour code	HS
Actuator	Push-button
Local signalling	Indicator light
Fixing mode	By screws
Material	PVC (polyvinyl chloride)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
Inrush current	20 A
Height	97.5 mm
Depth	43.6 mm
Embedding depth	31.6 mm
Width	34 mm
Mounting position	Vertical

Packing Units

Package 1 Weight	95.000 g
Package 1 Height	50.000 mm
Package 1 width	40.000 mm
Package 1 Length	100.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile