

Main

Range of product	C-Thru Saturn Series 4000
Product brand	Clipsal
Device presentation	Basic element
Dimmer type	Universal
Colour	Transparent

Complementary

Power consumption in VA	450 VA
Network frequency	50 Hz
Mounting support	Wall
Width	75 mm
Height	116 mm
Depth	56 mm
Embedding depth	34 mm





Environment

Standards	AS/NZS CISPR 15:2002 AS/NZS 3100 IEC 60669-2-1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	34.0 g
Package 1 Height	3 cm
Package 1 width	5.1 cm
Package 1 Length	9.4 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

