

Product data sheet

Characteristics

4062PBL-HS

Clipsal Saturn 4000, Push Button SwitchLED, 2 Gang, 250V, 16AX/20A



Main

Range of product	Saturn Series 4000
Product or component type	Push-button
Colour	Horizon silver
Product brand	Clipsal
Device presentation	Basic element with full cover plate



Complementary

Colour code	HS
Actuator	Push-button
Local signalling	Indicator light
Fixing mode	By screws
Material	PVC (polyvinyl chloride)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
Inrush current	20 A
Height	116 mm
Depth	43.6 mm
Embedding depth	31.6 mm
Width	75 mm
Mounting position	Vertical

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.6 cm
Package 1 Width	11.7 cm
Package 1 Length	7.6 cm
Package 1 Weight	206 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations