

Product data sheet

Characteristics

4063PBL-HS

Switch Saturn - Assembled - LED indicator - Vertical - 3-gang - 250 V - 20 A / 16 AX - Horizon Silver



Main

Range of product	Saturn Series 4000
Product or component type	Push-button
Colour	Horizon silver
Product brand	Clipsal
Device presentation	Basic element with full cover plate

Complementary

Colour code	HS
Actuator	Push-button
Local signalling	Indicator light
Fixing mode	By screws
Material	PVC (polyvinyl chloride)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
Inrush current	20 A
Height	116 mm
Depth	43.6 mm
Embedding depth	31.6 mm
Width	75 mm
Mounting position	Vertical

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.