

Product data sheet

Characteristics

408/3-WE

Clock Point Socket Outlet, Standard Series, 250VAC, 3 Pin

Main

Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Full cover plate

Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Flush
Fixing mode	By screws
Material	PVC (polyvinyl chloride)
Surface finish	Glossy
[In] rated current	5 A
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
Depth	30 mm
Length	106 mm
Width	59 mm
Fixing center	84 mm
Number of poles	1

Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	5.8 cm
Package 1 Length	10.5 cm
Package 1 Weight	40.6 g

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes