

Product data sheet

Characteristics

40RSM2

Clipsal Iconic, selector switch, mechanism, 4 positions, Off 1 Off 2, 10 A



Main

Range	Clipsal Iconic
Product or component type	Selector switch
Device application	Lighting
Colour tint	Vivid white
Quantity per set	Set of 20

Complementary

Device presentation	Mechanism
Control type	Rotary knob
Switch function	4 positions
Marking	0 - 1 - 0 - 2
Rated current	10 A
[Ue] rated operational voltage	250 V
Material	Plastic
Connections - terminals	Screw terminal
Height	23 mm
Width	23 mm
Depth	50 mm
Net weight	0.02 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	24.0 g
Package 1 Height	2.5 cm
Package 1 width	6 cm
Package 1 Length	10 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Weight	624.6 g
Package 2 Height	32.8 cm
Package 2 width	10.6 cm
Package 2 Length	14.6 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	240
Package 3 Weight	5760.0 g
Package 3 Height	33.5 cm

Package 3 width	26.1 cm
Package 3 Length	33.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile