

## Product data sheet

### Characteristics

# 412/110-WE

## Standard Series, Single Socket Outlet, 110VAC, 10A, 3 PIN, Surface Mount



### Main

Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

### Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Surface
Fixing mode	By screws
Material	Plastic
[In] rated current	10 A
[Ue] rated operational voltage	110 V AC
Depth	28 mm
Diameter	47 mm
Fixing center	35...38 mm
Number of poles	1

### Environment

Standards	AS 3109 AS 3100 AS/NZS 3112
-----------	-----------------------------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	28 cm
Package 1 Width	45 cm
Package 1 Length	45 cm
Package 1 Weight	0.052 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	70 cm
Package 2 Width	85 cm
Package 2 Length	110 cm
Package 2 Weight	0.26 kg
Unit Type of Package 3	CAR

Number of Units in Package 3	125
Package 3 Height	260 cm
Package 3 Width	220 cm
Package 3 Length	340 cm
Package 3 Weight	6.5 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations