

# Product data sheet

## Characteristics

# 413-WE

## SOCKET SURFACE 3PIN 10A 250V



### Main

Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

### Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Surface
Fixing mode	By screws
Material	Plastic
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
Depth	46 mm
Diameter	66 mm
Fixing center	50 mm
Number of poles	1




### Environment

Standards	AS 3109 AS 3100 AS/NZS 3112
-----------	-----------------------------------

### Packing Units

Package 1 Weight	0.086 kg
Package 1 Height	46.000 mm
Package 1 width	68.000 mm
Package 1 Length	88.000 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>

---

China RoHS Regulation

 [China RoHS Declaration](#)

---

Environmental Disclosure

 [Product Environmental Profile](#)

---