

Product data sheet

Characteristics

413/15-WE

SOCKET SURFACE 3PIN 15A 250V



Main

Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Surface
Fixing mode	By screws
Material	Plastic
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
Depth	46 mm
Diameter	66 mm
Fixing center	50 mm
Number of poles	1

Environment

Standards	AS 3109 AS 3100 AS/NZS 3112
-----------	-----------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	58 g
Package 1 Height	47 mm
Package 1 width	64 mm
Package 1 Length	65 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	0.65 kg
Package 2 Height	10.6 cm
Package 2 width	17 cm
Package 2 Length	17.1 cm

Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	6.4 kg
Package 3 Height	21 cm
Package 3 width	34.8 cm
Package 3 Length	44.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile